



H 1229 /...

Steckereinsatz
 Plug insert
 Connecteur

max. °C: 125
 DIN 16765 (HASCO Standard)
 VDE 0100



H12270/...
 H12271/...
 H12273/...




h1	l2	l1	Typ	I [A]	n1	Nr./No.
46,2	51	44	1	16	4	H 1229/1/16x 4
	64	57			8	8
51,2	84,5	77,5			16	16
	111	104			24	24

H 12290 /...

Steckereinsatz
 Plug insert
 Connecteur

DIN EN 61984, VDE 0627



H12270/...
 H12271/...
 H12273/...



h1	l2	l1	Typ	I [A]	n1	Nr./No.
32,4	51	44	1	16	6	H 12290/1/16x 6
	64	57			10	10
	84,5	77,5			16	16
	111	104			24	24