


Z802/...

Übergangskupplung, mit Absperrventil
 Adapter, with valve
 Adaptateur, avec valve d'arrêt


Mat.: 2.0401



Z802/...
 Z81/...
 Z811/...
 Z83/...
 Z830/...
 Z831/...
 Z90/...



Z80/... Z80PL/...
 Z801/... Z801PL/...
 Z805/...
 Z8051/...
 Z807/...
 Z80700/...
 Z808/...
 Z82/...



Medium	max. C°
Luft/air/air	200
Öl/oil/huile	120
Wasser/water/eau	100



Schlauchgrenzwerte können abweichen!
 Hose limits can differ!
 Les valeurs limites des tuyaux peuvent différer!

Typ	p [bar]	l2	l1	d6	d2	d4	d1	Nr./No.
2	25	15	20,5	10	6	5	9	Z802/ 5x 9
		14	30	17	8	9	13	9x13
1			36,5	22	6	13	9	13x 9
2		27			13		19	13x19
1		14	58	31	9	19	13	19x13


Z8021/...

Übergangskupplung, mit freiem Durchgang
 Adapter, open flow
 Adaptateur, à passage ouvert

Mat.: 2.0401



Z802/...
 Z81/...
 Z811/...
 Z83/...
 Z830/...
 Z831/...
 Z90/...



Z80/... Z80PL/...
 Z801/... Z801PL/...
 Z807/...
 Z808/...
 Z82/...



Medium	max. C°
Luft/air/air	200
Öl/oil/huile	120
Wasser/water/eau	100



Schlauchgrenzwerte können abweichen!
 Hose limits can differ!
 Les valeurs limites des tuyaux peuvent différer!

Typ	p [bar]	l2	l1	d6	d2	d4	d1	Nr./No.
2	25	14	30	17	8	9	13	Z8021/ 9x13
1			36,5	22	6	13	9	13x 9
2		27			13		19	13x19