


H 6132 / ...

Speziallegierung
Special alloy
Alliage special

H 61321 / ...

Speziallegierung beschichtet
Special alloy coated
Alliage special revêtu

Vario Shot®
Heißkanaldüse
Hotrunner nozzle
Buse á canal chaud



Pos.	Benennung	Designation	Désignation	Stück Quantity Pièce
1	Düsenkörper	Nozzle body	Corps de buse	1
2	Düsenkopf	Nozzle head	Tête de buse	1
3	Thermofühler	Thermocouple	Thermocouple	1
4	Heizung	Heater	Élément chauffant	1
5	Torpedospitze	Nozzle tip	Pointe torpédo	1
6	Vorkammer lang	Pre-chamber long	Écrou long	1
7	Zylinderstift	Dowel pin	Goupille cylindrique	1
8	Zylinderschraube	Socket head cap screw	Vis á tête cylindrique á six pans creux	4
9	Fühlerring	Sensor ring	Anneau de sonde	1

Ersatzteile/Spare parts/Pièces détachées

Pos.	1	2	3	4	5	6	7	8	9
H6132/...	H6001/...	H6101/...	H1295/6/...	H6002/...	H6030/...	H6090/...	Z25/...	Z31/...	H6003/...
H61321/...					H60301/...				
...25x 56	...25x 56	...25	...1x 55	...25x 56	...25	...25	...3x14	...3x 6	...25
63	63			63					
71	71		...1x 65	71					
80	80		...1x 75	80					
100	100		...1x 95	100					
125	125		...1x120	125					
140	140		...1x135	140					
160	160		...1x155	160					
...32x 63	...32x 63	...32	...1x 55	...32x 63	...32	...32	...5x14		...32
71	71		...1x 65	71					
80	80		...1x 75	80					
90	90		...1x 84	90					
100	100		...1x 95	100					
125	125		...1x120	125					
140	140		...1x135	140					
160	160		...1x155	160					
...40x 80	...40x 80	...40	...1x 75	...40x 80	...40	...40	...6x14	...4x 8	...40
90	90		...1x 84	90					
100	100		...1x 95	100					
112	112		...1x110	112					
125	125		...1x120	125					
140	140		...1x135	140					
160	160		...1x155	160					
180	180		...1x175	180					
200	200		...1x195	200					
...50x100	...50x100	...50	...1x 84	...50x100	...50	...50		...5x10	...50
112	112		...1x 95	112					
125	125		...1x110	125					
140	140		...1x135	140					
160	160		...1x155	160					
200	200		...1x195	200					
250	250		...1x235	250					
300	300		...1x285	300					

Vario Shot