


Z 1212 /...


Wärmeisolierplatte, eckig
 Thermal insulating sheet, rectangular
 Plaque isolante, carré

Mat.: Kunstharz/Glasfaser
 Synthetic resin/glass fibre
 Résine synth./ fibre de verre

max. 230°C
 $\lambda = 0,17 \text{ W/mK}$



2



Sicherheitsdatenblatt
 Safety data sheet
 Fiche de données de sécurité

b1	l1	s1	Nr./No.
095	095	5	Z 1212/095x 095x5
100	130		Z 1212/100x 130x5
156	156		Z 1212/156x 156x5
	196		196x5
	246		246x5
	296		296x5
	346		346x5
190	246		Z 1212/190x 246x5
	296	296x5	
	196	196	Z 1212/196x 196x5
246		246x5	
7		296	296x7
		346	346x7
		396	396x7
		446	446x7
		496	Z 1212/196x 496x7
546		546x7	
206	156	Z 1212/206x 156x7	
	196	196x7	
218	246	Z 1212/218x 246x7	
	296	296x7	
	396	396x7	
246	246	Z 1212/246x 246x7	
	296	296x7	
	346	346x7	
	396	396x7	
	446	Z 1212/246x 446x7	
	496	8,5	496x8,5



b1	l1	s1	Nr./No.
246	546	8,5	Z 1212/246x 546x8,5
	596		596x8,5
254	246		Z 1212/254x 246x8,5
276	246		Z 1212/276x 246x8,5
	296		296x8,5
296	296		Z 1212/296x 296x8,5
	346		346x8,5
	396		396x8,5
	446		446x8,5
	496		496x8,5
346	546	546x8,5	
	596	596x8,5	
	646	646x8,5	
	696	696x8,5	
	346	346	Z 1212/346x 346x8,5
		396	396x8,5
		446	446x8,5
		496	496x8,5
546		546x8,5	
396	596	596x8,5	
	646	646x8,5	
	696	696x8,5	
	796	796x8,5	
	396	396	Z 1212/396x 396x8,5
446		446x8,5	
496		496x8,5	
546		546x8,5	
596		596x8,5	
646		646x8,5	

Z 1212/...

Wärmeisolerplatte, eckig
 Thermal insulating sheet, rectangular
 Plaque isolante, carré

Mat.: Kunstharz/Glasfaser
 Synthetic resin/glass fibre
 Résine synth./fibre de verre

max. 230°C
 $\lambda = 0,17 \text{ W/mK}$



Sicherheitsdatenblatt
 Safety data sheet
 Fiche de données de sécurité

b1	l1	s1	Nr./No.		
396	696	8,5	Z 1212/396 x 696 x 8,5		
	796		796 x 8,5		
	896		896 x 8,5		
446	446	8,5	Z 1212/446 x 446 x 8,5		
	496		496 x 8,5		
	546		546 x 8,5		
	596		596 x 8,5		
	646		646 x 8,5		
	696		696 x 8,5		
	796		796 x 8,5		
	896		896 x 8,5		
	496		496	8,5	Z 1212/496 x 496 x 8,5
546		546 x 8,5			
596		596 x 8,5			
646		646 x 8,5			
696		696 x 8,5			
796		796 x 8,5			
896		896 x 8,5			
996		996 x 8,5			
546		546	8,5		Z 1212/546 x 546 x 8,5
	596	596 x 8,5			
	646	646 x 8,5			
	696	696 x 8,5			
	796	796 x 8,5			
	896	896 x 8,5			
	996	996 x 8,5			
	596	596		8,5	Z 1212/596 x 596 x 8,5
		646			646 x 8,5
696		696 x 8,5			

b1	l1	s1	Nr./No.
596	796	8,5	Z 1212/596 x 796 x 8,5
	896		896 x 8,5
	996		996 x 8,5
646	596	8,5	Z 1212/646 x 596 x 8,5
	646		646 x 8,5
	696		696 x 8,5
	746		746 x 8,5
	796		796 x 8,5
	896		896 x 8,5
	996		996 x 8,5
696	696	8,5	Z 1212/696 x 696 x 8,5
	746		746 x 8,5
	796		796 x 8,5
	896		896 x 8,5
	996		996 x 8,5
746	796	8,5	Z 1212/746 x 796 x 8,5
	896		896 x 8,5
	996		996 x 8,5
	996		996 x 8,5
796	796	8,5	Z 1212/796 x 796 x 8,5
	846		846 x 8,5
	896		896 x 8,5
	996		996 x 8,5
846	896	8,5	Z 1212/846 x 896 x 8,5
	996		996 x 8,5
	996		996 x 8,5
896	896	8,5	Z 1212/896 x 896 x 8,5
	996		996 x 8,5
	996		996 x 8,5

Firma/Company/Société: _____

Zuständig/Contact/Responsable: _____

Tel.: _____ Fax: _____

E-mail: _____ Datum/Date: _____

Bestellung/Order/Commande Nr./No.: _____ Anfrage/Quotation/Demande

Z121/.../S
Z1212/.../S

Wärmeisolerplatte
Thermal insulating sheet
Plaque d'isolation thermique

Toleranzbereich tolerance range zone de tolérance	b1 max.	l1 max.	s1 *	Druckfestigkeitsqualität Compressive strength quality Qualité de résistance à la compression	
				Z121/.../S	Z1212/.../S
+/- 0,15 mm	1200	2400	1 - 35	600 N/mm2	420 N/mm2

* abhängig von Plattengröße
depending on plate size
selon la grandeur de plaque



Stck./Pc.	Typ	b1	l1	s1	S	Beschichtung/coating/revêtement			
	Z121 /	x	x	/	S	<input type="checkbox"/>	ja/yes/oui	<input type="checkbox"/>	nein/no/non
	/	x	x	/	S	<input type="checkbox"/>		<input type="checkbox"/>	
	Z1212 /	x	x	/	S	<input type="checkbox"/>	ja/yes/oui	<input type="checkbox"/>	nein/no/non
	/	x	x	/	S	<input type="checkbox"/>		<input type="checkbox"/>	

Bitte Skizze/Zeichnung beifügen.

Please enclose diagram/drawing.

Veillez joindre un croquis/dessin.

Bearbeitungsdaten:

Machining data:

Données d'usinage:

3D step, Parasolid, 2D DXF oder DWG

3D step, Parasolid, 2D DXF or DWG

3D step, Parasolid, 2D DXF ou DWG

Senden Sie Ihre Anfrage bitte an:

Please send your quotation to:

Merci d'envoyer votre demande à:

Fax: 02351 957-320 oder/or/ou **Email: sonderanfertigungen@hasco.com**