


Z410/...

Auswerferstift, verdrehgesicherter Kopf, Form A
 Ejector pin, anti-twist head
 Ejecteur à tête cylindrique, tête indexée

Mat.: WAS (~ 1.2343)
 ~DIN 1530-1 A
 gehärtet/hardened/trempé




f1	r1	k1	a1	d2	d1	l1	Nr./No.
0,15	0,2	1,5	1,05	3	1,5	100	Z410/1,5x100
						125	125
						160	160
						200	200
0,25	2	1,5	4	2	80	Z410/2 x 80	
					100	100	
					125	125	
					160	160	
					200	200	
					250	250	
					315	315	
					400	400	
	2,2	1,5	4	2	100	Z410/2,2x100	
					125	125	
					160	160	
					200	200	
					315	315	
					2,5	100	Z410/2,5x100
					125	125	
					160	160	
0,3	1,75	5	2,5	100	Z410/2,5x100		
				125	125		
				160	160		
				200	200		
				250	250		
				315	315		
	2,7	1,75	5	2,5	100	Z410/2,7x100	
					125	125	
					160	160	
					200	200	
					250	250	
					315	315	
3	2	6	3	80	Z410/3 x 80		
				100	100		
				125	125		
				160	160		
				200	200		
				250	250		
				315	315		
				400	400		
				3,2	100	Z410/3,2x100	

f1	r1	k1	a1	d2	d1	l1	Nr./No.			
0,25	0,3	3	2	6	3,2	125	Z410/3,2x125			
						160	160			
						200	200			
						400	400			
						2,25	7	3,5	100	Z410/3,5x100
			125	125						
			160	160						
			200	200						
			250	250						
			2,35	0,3	3	2,35	7	3,7	100	Z410/3,7x100
125	125									
160	160									
200	200									
250	250									
2,5	0,3	3				2,5	8	4	80	Z410/4 x 80
									100	100
									125	125
									160	160
									200	200
2,6	0,3	3	2,6	8	4,2	80	Z410/4,2x180			
						100	100			
						125	125			
						160	160			
						200	200			
			2,75	0,3	3	2,75	8	4,5	100	Z410/4,5x100
									125	125

Z410/...

Auswerferstift, verdrehgesicherter Kopf, Form A
 Ejector pin, anti-twist head
 Ejecteur à tête cylindrique, tête indexée

Mat.: WAS (~ 1.2343)
 ~DIN 1530-1 A
 gehärtet/hardened/trempé



3


f1	r1	k1	a1	d2	d1	l1	Nr./No.
0,25	0,3	3	2,75	8	4,5	160	Z410/4,5x160
						200	200
						250	250
						315	315
						400	400
						500	500
			3,5	10	5	80	Z410/5 x 80
						100	100
						125	125
						160	160
						200	200
						250	250
		3,6		5,2	100	Z410/5,2x100	
					125	125	
					160	160	
					200	200	
					250	250	
					315	315	
		3,75	5,5	100	Z410/5,5x100		
				125	125		
				160	160		
				200	200		
				250	250		
				315	315		

f1	r1	k1	a1	d2	d1	l1	Nr./No.
0,5	0,5	5	4	12	6	315	Z410/6 x315
						400	400
						500	500
						630	630
						800	800
						4,1	6,2
			125	125			
			160	160			
			200	200			
			250	250			
			315	315			
			4,25	6,5	100	Z410/6,5x100	
		125			125		
		160			160		
		200			200		
		250			250		
		315			315		
		4,5		7	100	Z410/7 x100	
					125	125	
					160	160	
					200	200	
					250	250	
					315	315	
		4,75	7,5	100	Z410/7,5x100		
125	125						
160	160						
200	200						
250	250						
315	315						

Z410/...

Auswerferstift, verdrehgesicherter Kopf, Form A
 Ejector pin, anti-twist head
 Ejecteur à tête cylindrique, tête indexée

Mat.: WAS (~ 1.2343)
 ~DIN 1530-1 A
 gehärtet/hardened/trempé




f1	r1	k1	a1	d2	d1	l1	Nr./No.		
0,5	0,5	5	5	14	8	100	Z410/8 x100		
						125	125		
						160	160		
						200	200		
						250	250		
						315	315		
						400	400		
						500	500		
						630	630		
						800	800		
						5,1	8,2	100	Z410/8,2x100
								125	125
								160	160
								200	200
			250	250					
			315	315					
			400	400					
			5,25	8,5	100			Z410/8,5x100	
					125			125	
					160			160	
					200			200	
					250			250	
					315			315	
					400			400	
					630	630			
					5,5	9	100	Z410/9 x100	
							125	125	
			160	160					
200	200								
250	250								
315	315								
400	400								
500	500								
630	630								
5,75	9,5	100	Z410/9,5x100						
		125	125						

f1	r1	k1	a1	d2	d1	l1	Nr./No.			
0,5	0,5	5	5,75	14	9,5	160	Z410/ 9,5x160			
						200	200			
						250	250			
						315	315			
						400	400			
						500	500			
						6	16	10	100	Z410/10 x100
									125	125
									160	160
									200	200
			250	250						
			315	315						
			400	400						
			800	800						
			6,1	10,2	100				Z410/10,2x100	
					125				125	
					160	160				
					200	200				
					250	250				
					315	315				
					400	400				
					6,25	10,5	100	Z410/10,5x100		
							125	125		
							160	160		
			200	200						
			250	250						
			315	315						
			400	400						
			6,5	11			100	Z410/11 x100		
							125	125		
							160	160		
					200	200				
250	250									
315	315									
400	400									
500	500									
630	630									
800	800									
1000	1000									

Z410/...

Auswerferstift, verdrehgesicherter Kopf, Form A
 Ejector pin, anti-twist head
 Ejecteur à tête cylindrique, tête indexée

Mat.: WAS (~ 1.2343)
 ~DIN 1530-1 A
 gehärtet/hardened/trempé



3

f1	r1	k1	a1	d2	d1	l1	Nr./No.
0,5	0,5	5	6,5	16	11	400	Z410/11 x400
		0,8	7	18	12	100	Z410/12 x100
						125	125
						160	160
						200	200
						250	250
						315	315
						400	400
						500	500
						630	630
						800	800
			7,1		12,2	100	Z410/12,2x100
						125	125
						160	160
						200	200
						250	250
						315	315
						400	400
					12,5	100	Z410/12,5x100
						125	125
						160	160
						200	200
						250	250
						315	315
						400	400
						630	630
			8		13	200	Z410/13 x200
						400	400
			8,5	22	14	100	Z410/14 x100
						125	125
						160	160
						200	200
						250	250
						315	315
						400	400
						500	500

f1	r1	k1	a1	d2	d1	l1	Nr./No.
0,5	0,8	7	8,5	22	14	630	Z410/14 x630
						800	800
						9	15
						100	Z410/15 x100
						160	160
						250	250
						400	400
						9,5	16
						100	Z410/16 x100
						125	125
						160	160
						200	200
						250	250
						315	315
						400	400
						630	630
			10,5	24	18	100	Z410/18 x100
						160	160
						200	200
						250	250
						500	500
						1	8
			12,5	26	20	125	Z410/20 x125
						160	160
						200	200
						250	250
						315	315
						400	400
						500	500
						630	630
						10	15
			15	32	25	250	Z410/25 x250
						400	400
						18	40
			18	40	32	200	Z410/32 x200
						400	400