



Z4650 /...

Flachauswerfer, DLC, mit vier Eckenradien
 Flat ejector pin, DLC, with four corner radii
 Ejecteur lame, DLC, avec 4 rayons d'angle

Mat.: WS (\approx 1.2516 - 60HRC)
 DIN ISO 8693 (DIN 1530-4)





r1	k1	l3	l2	d2	d1	b1	s1	l1	Nr./No.			
0,3	3	30	100	10	5	4,5	1	200	Z4650/4,5x1 x200			
			125					250				
			160					315				
		-	30	40	10	5	4,5	1,2	80	Z4650/4,5x1,2x 80		
				50					100			
				60					125			
			-	30	80	10	5	4,5	1,5	160	Z4650/4,5x1,5x 80	
					100					200		
					125					250		
					160					315		
					80					100		
					100					200		
			0,5	5	-	40	12	6	5,5	1	80	Z4650/5,5x1 x 80
						50					100	
						60					125	
		30			80	12	6	5,5	1	160	Z4650/5,5x1 x 80	
					100					200		
					125					250		

Z4650 /...

Flachauswerfer, DLC, mit vier Eckenradien
 Flat ejector pin, DLC, with four corner radii
 Ejecteur lame, DLC, avec 4 rayons d'angle

Mat.: WS (\approx 1.2516 - 60 HRC)
 DIN ISO 8693 (DIN 1530-4)





r1	k1	l3	l2	d2	d1	b1	s1	l1	Nr./No.	
0,5	5	-	40	12	6	5,5	1,2	80	Z4650/5,5x1,2x 80	
			50					100	100	
			60					125	125	
			80					160	160	
			100					200	200	
			125					250	250	
			160					315	315	
			50					1,5	100	Z4650/5,5x1,5x100
			60						125	125
			80						160	160
			100						200	200
			125						250	250
			160						315	315
			50					2	100	Z4650/5,5x2 x100
		60	125	125						
		80	160	160						
		100	200	200						
		125	250	250						
		160	315	315						
		6	125	14	8	7,5	1,2	100	Z4650/7,5x1,2x100	
		30	160						125	
		50	125						125	
		60	160						160	
		80	200						200	
		100	250						250	
		125	315						315	
		160	1,5						125	Z4650/7,5x1,5x125
		60							160	160
		80							200	200
		100							250	250
125	315	315								
160	125	125								

Z4650 /...

Flachauswerfer, DLC, mit vier Eckenradien
 Flat ejector pin, DLC, with four corner radii
 Ejecteur lame, DLC, avec 4 rayons d'angle

Mat.: WS ($\approx 1.2516 - 60\text{HRC}$)
 DIN ISO 8693 (DIN 1530-4)



r1	k1	l3	l2	d2	d1	b1	s1	l1	Nr./No.		
0,5	5	30	80	14	8	7,5	1,5	160	Z4650/ 7,5x1,5x160		
			100					200			
			125					250			
			160					315			
			80					160	Z4650/ 7,5x2 x160		
			100					200			
		8	125	250							
			160	315							
			30	80	16	10	9,5	1,5	160	Z4650/ 9,5x1,5x160	
			100	200							
			125	250							
			160	315							
		10	160	200					Z4650/ 9,5x2 x200		
		30	100	250							
		0,8	7		100	18	12	11,5	2,5	200	Z4650/11,5x2 x200
					125					250	
160	315										
100	200				Z4650/11,5x2,5x200						
125	250										
160	315										