

Firma/Company/Société: _____

Zuständig/Contact/Responsable: _____



Tel.: _____ Fax: _____ Datum/Date: _____

Bestellung/Order/Commande Nr./No.: _____ Anfrage/Quotation/Demande

Z466 /... / S

Flachauswerfer
Flat ejector pin
Ejecteur lame

Mat.: WS* (≈ 1.2516) / 60 ± 2 HRC
 Mat.: WAS** (≈ 1.2343) ≥ 950 HV0,3
 Mat.:



*** ≥ 0,15
 keine Angabe = scharfkantig
 not specified = sharp-edged
 sans indication = à arêtes vives

| Stck./ Pc. | Typ | d1 | l1 | a/c | b/c | l4 | S | r1 | r2 | r3 | r4 | l1 | a | b | c | l4 max. | d2 | k | r |
|---------------|------------|----|----|-----|-----|----|---|----|----|----|----|-------|-------|-------|-------|------------|----|---|-----|
| | Z466 / 3 | x | / | x | x | / | S | | | | | ≙ 40 | ≙ 2 | ≙ 0,6 | ≙ 1,5 | 80 | 6 | 3 | 0,3 |
| | / 3 | x | / | x | x | / | S | | | | | ↓ | ↓ | ↓ | ↓ | | | | |
| | / 3 | x | / | x | x | / | S | | | | | ≙ 250 | ≙ 2,5 | ≙ 1 | ≙ 2 | | | | |
| | Z466 / 3,5 | x | / | x | x | / | S | | | | | ≙ 80 | ≙ 2 | ≙ 0,6 | ≙ 1,5 | 7 | | | |
| | / 3,5 | x | / | x | x | / | S | | | | | ↓ | ↓ | ↓ | ↓ | | | | |
| | / 3,5 | x | / | x | x | / | S | | | | | ≙ 250 | ≙ 3 | ≙ 1 | ≙ 2,3 | | | | |
| | Z466 / 4 | x | / | x | x | / | S | | | | | ≙ 40 | ≙ 2,5 | ≙ 0,6 | ≙ 1,5 | 100 | 8 | | |
| | / 4 | x | / | x | x | / | S | | | | | ↓ | ↓ | ↓ | ↓ | | | | |
| | / 4 | x | / | x | x | / | S | | | | | ≙ 400 | ≙ 3,5 | ≙ 1,2 | ≙ 2,7 | | | | |
| | Z466 / 4,5 | x | / | x | x | / | S | | | | | ≙ 40 | ≙ 2,5 | ≙ 0,8 | ≙ 1,5 | | | | |
| | / 4,5 | x | / | x | x | / | S | | | | | ↓ | ↓ | ↓ | ↓ | | | | |
| | / 4,5 | x | / | x | x | / | S | | | | | ≙ 315 | ≙ 4 | ≙ 1,2 | ≙ 3 | | | | |
| | Z466 / 5 | x | / | x | x | / | S | | | | | ≙ 40 | ≙ 3 | ≙ 1 | ≙ 1,5 | 10 | | | |
| | / 5 | x | / | x | x | / | S | | | | | ↓ | ↓ | ↓ | ↓ | | | | |
| | / 5 | x | / | x | x | / | S | | | | | ≙ 400 | ≙ 4,5 | ≙ 1,3 | ≙ 3,4 | | | | |
| | Z466 / 5,5 | x | / | x | x | / | S | | | | | ≙ 60 | ≙ 3 | ≙ 1 | ≙ 2 | | | | |
| | / 5,5 | x | / | x | x | / | S | | | | | ↓ | ↓ | ↓ | ↓ | | | | |
| | / 5,5 | x | / | x | x | / | S | | | | | ≙ 315 | ≙ 5 | ≙ 1,3 | ≙ 3,7 | | | | |
| | Z466 / 6 | x | / | x | x | / | S | | | | | ≙ 40 | ≙ 3 | ≙ 1 | ≙ 2,5 | 125 | 12 | 5 | 0,5 |
| | / 6 | x | / | x | x | / | S | | | | | ↓ | ↓ | ↓ | ↓ | | | | |
| | / 6 | x | / | x | x | / | S | | | | | ≙ 400 | ≙ 5,5 | ≙ 1,3 | ≙ 4,1 | | | | |
| | Z466 / 6,5 | x | / | x | x | / | S | | | | | ≙ 80 | ≙ 3 | ≙ 1,2 | ≙ 2,5 | | | | |
| | / 6,5 | x | / | x | x | / | S | | | | | ↓ | ↓ | ↓ | ↓ | | | | |
| | / 6,5 | x | / | x | x | / | S | | | | | ≙ 315 | ≙ 6 | ≙ 2 | ≙ 4,4 | | | | |
| | Z466 / 7 | x | / | x | x | / | S | | | | | ≙ 80 | ≙ 4 | ≙ 1,2 | ≙ 3 | | | | |
| | / 7 | x | / | x | x | / | S | | | | | ↓ | ↓ | ↓ | ↓ | | | | |
| | / 7 | x | / | x | x | / | S | | | | | ≙ 315 | ≙ 6 | ≙ 2,5 | ≙ 4,8 | | | | |

Firma/Company/Société: _____

Zuständig/Contact/Responsable: _____



Tel.: _____ Fax: _____ Datum/Date: _____

Bestellung/Order/Commande Nr./No.: _____ Anfrage/Quotation/Demande

Z466 /.../ S

Flachauswerfer
Flat ejector pin
Ejecteur lame

Mat.: WS* (≈ 1.2516) / 60 ± 2 HRC
 Mat.: WAS** (≈ 1.2343) ≥ 950 HV0,3
 Mat.:



*** ≥ 0,15
 keine Angabe = scharfkantig
 not specified = sharp-edged
 sans indication = à arêtes vives

| Stck./ Pc. | Typ | d1 | l1 | a/c | b/c | l4 | S | r1 | r2 | r3 | r4 | l1 | a | b | c | l4 max. | d2 | k | r |
|---------------|--------|------|----|-----|-----|-----|---|----|----|----|----|-------|------|-------|--------|------------|----|---|-----|
| | Z466 / | 8 x | / | x | x | / S | | | | | | ≡ 40 | ≡ 4 | ≡ 1,2 | ≡ 3 | 155 | 14 | 5 | 0,5 |
| | / | 8 x | / | x | x | / S | | | | | | ↓ | ↓ | ↓ | ↓ | | | | |
| | / | 8 x | / | x | x | / S | | | | | | ≡ 400 | ≡ 7 | ≡ 3 | ≡ 5,5 | | | | |
| | Z466 / | 9 x | / | x | x | / S | | | | | | ≡ 100 | ≡ 5 | ≡ 1,5 | ≡ 3,5 | | | | |
| | / | 9 x | / | x | x | / S | | | | | | ↓ | ↓ | ↓ | ↓ | | | | |
| | / | 9 x | / | x | x | / S | | | | | | ≡ 315 | ≡ 8 | ≡ 3 | ≡ 6,2 | | | | |
| | Z466 / | 10 x | / | x | x | / S | | | | | | ≡ 60 | ≡ 5 | ≡ 1,5 | ≡ 3,5 | 200 | 16 | | |
| | / | 10 x | / | x | x | / S | | | | | | ↓ | ↓ | ↓ | ↓ | | | | |
| | / | 10 x | / | x | x | / S | | | | | | ≡ 400 | ≡ 9 | ≡ 3,5 | ≡ 7 | | | | |
| | Z466 / | 11 x | / | x | x | / S | | | | | | ≡ 100 | ≡ 6 | ≡ 2 | ≡ 4 | | | | |
| | / | 11 x | / | x | x | / S | | | | | | ↓ | ↓ | ↓ | ↓ | | | | |
| | / | 11 x | / | x | x | / S | | | | | | ≡ 315 | ≡ 10 | ≡ 3,5 | ≡ 7,6 | | | | |
| | Z466 / | 12 x | / | x | x | / S | | | | | | ≡ 80 | ≡ 6 | ≡ 2 | ≡ 4 | | 18 | 7 | 0,8 |
| | / | 12 x | / | x | x | / S | | | | | | ↓ | ↓ | ↓ | ↓ | | | | |
| | / | 12 x | / | x | x | / S | | | | | | ≡ 400 | ≡ 11 | ≡ 3,5 | ≡ 8,3 | | | | |
| | Z466 / | 14 x | / | x | x | / S | | | | | | ≡ 100 | ≡ 7 | ≡ 2 | ≡ 5 | | 22 | | |
| | / | 14 x | / | x | x | / S | | | | | | ↓ | ↓ | ↓ | ↓ | | | | |
| | / | 14 x | / | x | x | / S | | | | | | ≡ 400 | ≡ 13 | ≡ 4 | ≡ 9,7 | | | | |
| | Z466 / | 16 x | / | x | x | / S | | | | | | ≡ 100 | ≡ 8 | ≡ 2 | ≡ 5 | | | | |
| | / | 16 x | / | x | x | / S | | | | | | ↓ | ↓ | ↓ | ↓ | | | | |
| | / | 16 x | / | x | x | / S | | | | | | ≡ 400 | ≡ 16 | ≡ 4 | ≡ 11,2 | | | | |
| | Z466 / | 18 x | / | x | x | / S | | | | | | ≡ 160 | ≡ 9 | ≡ 3 | ≡ 6 | | 24 | | |
| | / | 18 x | / | x | x | / S | | | | | | ↓ | ↓ | ↓ | ↓ | | | | |
| | / | 18 x | / | x | x | / S | | | | | | ≡ 315 | ≡ 17 | ≡ 4,5 | ≡ 12,6 | | | | |
| | Z466 / | 20 x | / | x | x | / S | | | | | | ≡ 160 | ≡ 10 | ≡ 3 | ≡ 8 | | 26 | 8 | 1 |
| | / | 20 x | / | x | x | / S | | | | | | ↓ | ↓ | ↓ | ↓ | | | | |
| | / | 20 x | / | x | x | / S | | | | | | ≡ 400 | ≡ 19 | ≡ 5 | ≡ 14 | | | | |